

Black Aluminum ATA/133 Removable Hard Drive Mobile Rack Drawer

StarTech ID: DRW150ATABK



StarTech.com's DRW150ATABK is an ideal removable drive enclosure for switching between multiple operating systems, making high-speed, high-capacity backups or for other applications requiring frequent removal and insertion of mobile hard drives. This removable storage solution features a locking mechanism to prevent the drive from being accidentally removed while in use and a 25K Insertion Rating.

The DRW150ATABK's compact, durable aluminum construction makes the drive enclosure easy to transport while helping to dissipate heat away from the drive. The DRW150ATABK is interchangeable with StorCase ATA(IDE) models S21B109 & SC21B109 and model RJR110.

Applications

- Removable drive drawers can be used in homes, at work, offices and in schools
- Mobile solution for high-capacity databases and large applications
- A fast and easy way to make backup copies of your files, applications and company's critical data

Features

- Secure and affordable solution to store and transfer data
- Ball-bearing fan maintains optimum cooling and increased air flow
- LED indicators continuously show the operating status of the drive drawer
- Key lock mechanism prevents a hard drive from being accidentally removed while in operation
- Screw type stopper to avoid cover vibration while the HDD is working
- Supports hard drive ATA66/ATA100 & ATA133 with data transfer rates up to 133 MB/s
- Supports hot swap and hot plug-in
- Compatibility with PC and MAC's

Technical Specifications

Warranty	2 Years
Key Lock	Yes
Fans	1 - 40 mm
Connector Type(s)	1 - IDE (40 Pin; EIDE/PATA) Female
Connector Type(s)	1 - IDE (40 Pin; EIDE/PATA) Male
Connector Type(s)	1 - LP4 (4 pin; Molex Large Drive Power) Female
Connector Type(s)	1 - LP4 (4 pin; Molex Large Drive Power) Male
General Specifications	
General Specifications	1.57 x 1.57 x 0.39 Inches (40 x 40 x 10 mm)
General Specifications	1.90 Lbs (0.86 Kgs)
General Specifications	220 x 148 x 41
General Specifications	9.00 x 5.75 x 1.61
General Specifications	All 3.5-Inch IDE Hard Drives
General Specifications	Aluminum
General Specifications	Black
General Specifications	CE
General Specifications	Drive Activity & Drive Power
General Specifications	Header: 40 Pin Female & LP4: 4 Pin Female
General Specifications	Header: 40 Pin Male & LP4: 4 Pin Female
General Specifications	PC or Mac with a 5.25 Inch Drive Bay
General Specifications	Plastic
General Specifications	Unit is model specific and is not meant for use with different models of drive drawer unless otherwise stated
Color	Black
Enclosure Type	Aluminum
Product Length	8.7 in [220 mm]
Product Width	5.8 in [148 mm]
Product Height	1.6 in [41 mm]
Product Weight	30.4 oz [860 g]
LED Indicators	1 - Activity
LED Indicators	1 - Power
Shipping (Package) Weight	2 lb [0.9 kg]

Certifications, Reports and Compatibility

