

## Black Aluminum 5.25in Rugged SATA Hard Drive Mobile Rack Drawer

StarTech ID: DRW150SATBK



This high quality Removable SATA Hard Drive Drawer/Mobile Rack delivers a professional-grade hot-swap solution, allowing you to quickly swap SATA hard drives in/out of a computer without having to open the computer case. With support for SATA speeds up to 6 Gbps, the mobile rack is fully compatible with RAID installations to ensure maximum performance and versatility for enhanced storage applications.

Simply install the drive bay into a 5.25in bay on the host computer, then mount a 3.5in SATA HDD into the (removable) caddy. Connecting the SATA hard drive to the computer is as easy as inserting the caddy into the drive bay, which can be locked to prevent unauthorized removal of the drive. Features a front panel ball bearing fan, aluminum construction and 25K insertion rating. Backed by StarTech.com's 2-year warranty.

**This product is interchangeable as a replacement for StorCase SATA models S21J111, SC21J111 and RJR110.**

### Applications

- Add additional hot-swap bays to a server or workstation computer
- Replace or upgrade old IDE backplane with a SATA backplane
- System builders who need to image many drives simultaneously and quickly
- Environments where drives need to be replaced/removed regularly, without external protection for the drives required after removal
- Be able to replace/remove individual drives from a storage array with minimal or no system down time

## Features

- Fits a single SATA drive into a front accessible 5.25" bay
- Heavy duty aluminum construction for the drive caddy and bay
- Key lockable drive caddy
- Rubber shock absorbers
- 25,000+ insertion rating
- 40mm ball bearing cooling fan
- Dust resistant door on bay unit
- Power and Activity LED indicators
- Fully supports SATA revision 1/2/3 (1.5/3.0/6.0 Gbps) drives and controllers
- Supports 3.5" form factor SATA hard drives

## Technical Specifications

Warranty	2 Years
Key Lock	Yes
Drive Size	3.5in
Drive Type	SATA
Fans	1 - 40 mm
Fan Bearing Type	Ball Bearing
Drive Connectors	1 - SATA (7 pin; Data) Receptacle
Drive Connectors	1 - SATA Power (15 pin) Receptacle
Host Connectors	1 - LP4 (4 pin; Molex Large Drive Power) Male
Host Connectors	1 - SATA (7 pin; Data) Plug
Host Connectors	1 - SATA Power (15 pin) Receptacle
Color	Black
Enclosure Type	Aluminum
Product Length	7.5 in [190 mm]
Product Width	5.8 in [147 mm]
Product Height	1.6 in [41 mm]
Product Weight	30.4 oz [860 g]
LED Indicators	1 - Activity (Yellow)
LED Indicators	1 - Power (Green)
System and Cable Requirements	PC or Mac with a 5.25 Inch Drive Bay

**Note** Unit is model specific and is not meant for use with different models of drive drawer unless otherwise stated

Shipping (Package) Weight	1.8 lb [0.8 kg]
Included in Package	1 - Mobile Rack Caddy
Included in Package	1 - 5.25" Mobile Rack Bay
Included in Package	1 - SATA Cable
Included in Package	2 - Key
Included in Package	1 - Screw Kit
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

