

230 foot (70 meter) Active DVI Monitor Extension Cable

StarTech ID: *DVIAEXT70*



Extend the range of your DVI-enabled displays without losing signal quality! StarTech.com's Active DVI extension cables deliver crystal-clear digital images instantly – with a sharper, stronger signal than standard VGA monitor cables. Even over longer distances the quality of your digital images is preserved. Backed by StarTech.com's 2-year warranty and FREE lifetime tech support.

Applications

- Conference Rooms
- Hospitals
- Educational Institutions
- Transportation Industry

Features

- High 1600 x 1200 pixel UXGA resolution
- Supports hot plugging of DVI display devices for quick setup
- Immune to EMI and RFI with crystal-clear signal quality across long distances
- High speed digital transmission up to 1.25 Gbits/sec
- Compliant with the DVI 1.0 standard

Technical Specifications

Warranty	2 Years
Connector A	1 - DVI-D (19 pin) Male
Connector B	1 - DVI-D (19 pin) Male
General Specifications	
General Specifications	1600 x 1200 pixels (UXGA)
General Specifications	18-pin DVI-D (Male) Color: Orange
General Specifications	18-pin DVI-D (Male)
General Specifications	230 feet (70 meters)
General Specifications	DVI-D (True Digital Video)
General Specifications	H-PCF Graded multi-mode fiber Maximum Resolution: SXGA, 1280 x 1024
General Specifications	HDCP compliant
General Specifications	Note that this product is not intended for use with widescreen displays.
Color	Orange
Product Length	2755.9 in [70000 mm]
Shipping (Package) Weight	11.2 lb [5.1 kg]

Certifications, Reports and Compatibility

