

15ft 4-in-1 USB Dual Link DVI-D KVM Switch Cable w/ Audio & Microphone

StarTech ID: DVID4N1USB15



The DVID4N1USB15 15ft 4-in-1 USB Dual Link DVI-D KVM Switch Cable w/ Audio & Microphone integrates dual link DVI video quality with USB mouse and keyboard, 3.5mm audio out and microphone connections into a single, compact cable.

The four-in-one DVI KVM cable is a cost-effective and convenient solution that's suitable for use with dual link DVI supported USB KVM switches, allowing you to share a USB peripheral set between two computers configured for high definition output.

Backed by a StarTech.com Lifetime Warranty.

Works with:

Compatible StarTech.com KVMs can be found under the Accessories section.

Aten models (CS1642, CS1644, CS1784, CS1782, CS1762, CS1764)

Avocent models (2SVDVI10-001, 4SVDVI10-001, SV4UAD, SC420, SC440, SC540)

Belkin models (F1DN102D, F1DN104D, F1DD102L, F1DD104L)

Cables to go models (52047, 52048)

Applications

- Connects a computer to a Dual Link DVI + USB KVM switch with audio and mic support

Features

- Combines 4 peripheral cables into one
- Dual Link DVI-D signal is supported
- Meets and exceeds all DVI-D and USB 2.0 specifications
- Supports DVI-D Maximum clock frequency in dual link mode up to 7.92 Gbit/s)

Technical Specifications

| | |
|---------------------------|--|
| Warranty | Lifetime |
| Cable Jacket Type | PVC - Polyvinyl Chloride |
| Connector A | 1 - DVI-D (25 pin) Male |
| Connector A | 1 - USB A (4 pin) Male |
| Connector A | 2 - 3.5 mm Mini-Jack (3 Position) Male |
| Connector B | 1 - DVI-D (25 pin) Male |
| Connector B | 1 - USB B (4 pin) Male |
| Connector B | 2 - 3.5 mm Mini-Jack (3 Position) Male |
| Color | Black |
| Cable Length | 15 ft [4.6 m] |
| Product Length | 15 ft [4.6 m] |
| Product Width | 1.6 in [39.5 mm] |
| Product Height | 0.6 in [15.5 mm] |
| Product Weight | 30.9 oz [874 g] |
| Shipping (Package) Weight | 894 |
| Included in Package | 1 - 4-in-1 DVI-D USB KVM Cable |

Certifications, Reports and Compatibility

