

15 ft Dual Link Monitor DVI-D Extension Cable - M/F

StarTech ID: *DVIDDMF15*



This DVI-D extension cable provides one DVI-D dual link Male connector and one DVI-D dual link Female connector to create a reliable way to extend your DVI-D (dual link) cable connection.

With support for high speed digital video data transmissions up to 9.9Gbps, the extension cable is suited for high resolution applications on your panel display, digital projector, or HDTV.

Expertly designed and constructed of only top quality materials, this high performance DVI-D dual link extension cable is backed by StarTech.com's Lifetime Warranty.

Applications

- Compatible with Flat Panel Displays, Digital CRT Displays, Projectors and HDTV
- Easily connect your PC to a HDTV, Projector and CRT Displays

Features

- Supports hot plugging of DVI display devices
- Compliant with DVI DDWG Standards
- High speed digital transmission rate of up to 9.9 Gbits/sec
- Dual link digital signalling allows high speed digital data transmission
- Compatible with PC and Mac computer systems
- DVI-D Dual Link Display Cable supports digital displays only

Technical Specifications

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Type	PVC - Polyvinyl Chloride
Number of Ferrites	1
Connector A	1 - DVI-D (25 pin) Male
Connector B	1 - DVI-D (25 pin) Female
Color	Black
Cable Length	15 ft [4.6 m]
Product Weight	1.1 lb [0.5 kg]
Shipping (Package) Weight	1.1 lb [0.5 kg]
Included in Package	1 - 15 ft Dual Link Monitor DVI-D Extension Cable - M/F

Certifications, Reports and Compatibility

