

## 6 ft DVI-D Dual Link Digital Video Monitor Cable - M/F

StarTech ID: *DVIDDMF6*



This DVI-D dual link extension cable provides one DVI-D dual link Male connector and one DVI-D dual link Female connector to create a reliable way to extend your DVI-D (dual link) cable connection.

With support for high speed digital video data transmissions up to 9.9Gbps, the extension cable is suited for high resolution applications on your panel display, digital projector, or HDTV crystal clear.

Expertly designed and constructed of only top quality materials, this high performance DVI-D dual link extension cable is backed by StarTech.com's Lifetime Warranty.

### Applications and Solutions

- Compatible with Flat Panel Displays, Digital CRT Displays, Projectors and HDTV
- Easily connect your PC to a HDTV, Projector and CRT Displays

## Features

- Compatible with PC and Mac computer systems
- Compliant with DVI DDWG Standards
- Dual link digital signalling allows high speed digital data transmission
- DVI-D Dual Link Display Cable supports digital displays only
- High speed digital transmission rate of up to 9.9 Gbits/sec
- Supports hot plugging of DVI display devices

## Technical Specifications

- Warranty: Lifetime warranty
- Color: Black
- Carton Quantity: 60
- Shipping (Package) Weight: 0.55 lb [0.25 kg]
- Cable Length: 6 ft [1.83 m]
- Connector A: 1 - 25 pin DVI-D (Dual Link) Female
- Connector B: 1 - 25 pin DVI-D (Dual Link) Male
- Wire Gauge: 28 AWG

