

## 2m DVI-D Dual Link Monitor Cable - M/M

StarTech ID: *DVIDDMM2M*



The DVIDDMM2M 2-meter DVI-D dual link cable features 2 male DVI digital (dual link) connectors and supports high-speed data transmissions of up to 9.9Gbps between DVI digital devices such as HDTVs, Blu-Ray players, DVD players and more.

StarTech.com DVI-D cables are expertly designed and constructed of only top quality materials to ensure a long-lasting, high quality connection that helps keep the resolution on your panel display, digital projector, or HDTV crystal clear.

A high quality digital video solution, the 2-meter DVI-D dual link cable is backed by StarTech.com's Lifetime Warranty.

\*Please note: DVI-D Dual Link display cables support digital displays only.

### Applications

- Compatible with Flat Panel Displays, Digital CRT Displays, Projectors and HDTV

### Features

- DVIDDWWG Standards compliant
- High speed digital transmission rate of up to 9.9 Gbits/sec
- Supports hot plugging of DVI display devices
- Ferrite core eliminates EMI interference

## Technical Specifications

Warranty	Lifetime
Number of Conductors	24
Connector Plating	Nickel
Cable Jacket Type	PVC - Polyvinyl Chloride
Cable Shield Type	Aluminum-Mylar Foil with Braid
Fire Rating	CMG Rated (General Purpose)
Number of Ferrites	2
Industry Standards	DVI DDWG Standard
Connector A	1 - DVI-D (25 pin) Male
Connector B	1 - DVI-D (25 pin) Male
Color	Black
Connector Style	Straight
Wire Gauge	28 AWG
Cable Length	6.6 ft [2 m]
Cable OD	0.3 in [8.6 mm]
Product Weight	6.8 oz [193 g]
Package Quantity	1
Shipping (Package) Weight	198
Included in Package	1 - 2m DVI-D Dual Link Digital Video Monitor Cable - M/M

## Certifications, Reports and Compatibility

