

40 ft DVI-D Dual Link Digital Video Monitor Cable - M/M

StarTech ID: *DVIDDMM40*



This 40ft DVI-D dual link cable features two male DVI-D connectors and supports high speed data transmissions of up to 9.9Gbps to provide a stronger, faster signal that keeps the resolution on your panel display, digital projector, or HDTV crystal clear.

Expertly designed and constructed of only top quality materials, the DVIDDMM40 DVI-D dual link cable is backed by our Lifetime Warranty.

Applications and Solutions

- Compatible with Flat Panel Displays, Digital CRT Displays, Projectors and HDTV
- Easily connect your PC to a HDTV, Projector and CRT Displays

Features

- Compatible with PC and Mac computer systems
- Compliant with DVI DDWG Standards
- Dual link digital signalling allows high speed digital data transmission
- DVI-D Dual Link Display Cable supports digital displays only
- High speed digital transmission rate of up to 9.9 Gbits/sec
- Supports hot plugging of DVI display devices

Technical Specifications

- Warranty: Lifetime warranty
- Color: Black
- Carton Quantity: 5
- Shipping (Package) Weight: 2.43 lb [1.1 kg]
- Cable Length: 40 ft [12.2 m]
- Connector A: 1 - 25 pin DVI-D (Dual Link) Male
- Connector B: 1 - 25 pin DVI-D (Dual Link) Male
- Industry Standards: DVI DDWG Standard
- Wire Gauge: 28 AWG

