

40 ft DVI-D Dual Link Digital Video Monitor Cable - M/M

StarTech ID: *DVIDDMM40*



This 40ft DVI-D dual link cable features two male DVI-D connectors and supports high speed data transmissions of up to 9.9Gbps to provide a stronger, faster signal that keeps the resolution on your panel display, digital projector, or HDTV crystal clear.

Expertly designed and constructed of only top quality materials, the DVIDDMM40 DVI-D dual link cable is backed by our Lifetime Warranty.

Applications

- Compatible with Flat Panel Displays, Digital CRT Displays, Projectors and HDTV
- Easily connect your PC to a HDTV, Projector and CRT Displays

Features

- Supports hot plugging of DVI display devices
- Compliant with DVI DDWG Standards
- High speed digital transmission rate of up to 9.9 Gbits/sec
- Dual link digital signalling allows high speed digital data transmission
- Compatible with PC and Mac computer systems
- DVI-D Dual Link Display Cable supports digital displays only

Technical Specifications

Warranty	Lifetime
Connector Plating	Nickel
Industry Standards	DVI DDWG Standard
Connector A	1 - DVI-D (25 pin) Male
Connector B	1 - DVI-D (25 pin) Male
Color	Black
Wire Gauge	28 AWG
Cable Length	40 ft [12.2 m]
Product Weight	2.4 lb [1.1 kg]
Shipping (Package) Weight	2.4 lb [1.1 kg]
Included in Package	1 - 40 ft DVI-D Dual Link Digital Video Monitor Cable - M/M

Certifications, Reports and Compatibility

