

## 6 ft DVI-D Dual Link Cable M/M

StarTech ID: *DVIDDMM6*



The DVIDDMM6, 6-foot DVI-D dual link cable features two male DVI digital (dual link) connectors and supports high speed data transmissions of up to 9.9Gbps between DVI digital devices such as HDTVs, Blu-Ray players, DVD players and more.

StarTech.com DVI-D cables are expertly designed and constructed of only top quality materials to ensure a long lasting, high quality connection that helps keep the resolution on your panel display, digital projector, or HDTV crystal clear.

A high quality digital video solution, the DVI-D dual link cable is backed by StarTech.com's Lifetime Warranty.

### Applications

- Compatible with Flat Panel Displays, Digital CRT Displays, Projectors and HDTV
- Easily connect your PC to a HDTV, Projector and CRT Displays
- Compatible with PC and Mac® computer systems
- DVI-D Dual Link Display Cable supports digital displays only

### Features

- Compliant with DVI DDWG Standards
- High speed digital transmission rate of up to 9.9 Gbits/sec
- Supports hot plugging of DVI display devices
- Ferrite core eliminates EMI interference

## Technical Specifications

Warranty	Lifetime
Connector Plating	Nickel
Cable Shield Type	Aluminum-Mylar Foil with Braid
Industry Standards	DVI DDWG Standard
Connector A	1 - DVI-D (25 pin) Male
Connector B	1 - DVI-D (25 pin) Male
Color	Black
Wire Gauge	28 AWG
Cable Length	6 ft [1.8 m]
Product Weight	7.7 oz [218 g]
Shipping (Package) Weight	0.7 lb [0.3 kg]
Included in Package	1 - 6 ft DVI-D Dual Link Cable - M/M

## Certifications, Reports and Compatibility

