

## 10 ft DVI-D Single Link Monitor Extension Cable - M/F

StarTech ID: *DVIDSMF10*



This 10ft single-link DVI-D extension cable offers a high quality connection that allows you to get the most out of your high-end digital video card and flat-panel digital LCD monitor.

With DVI-D technology, no digital-to-analog conversion is necessary, so the signal is delivered faster and stronger than a standard monitor cable signal. The plug and play-compatible, all-digital connection provided by this DVI-D extension cable is also ideal for connecting laptop computers to digital projectors for crystal-clear presentations.

By interfacing two digital signals directly, you'll experience faster, higher-quality images. This single-link cable works with virtually any DVI digital flat panel LCD monitor and allows high-speed DVI video data transmissions of up to 4.95 Gbps.

### Applications

- Compatible with Flat Panel Displays, Digital CRT Displays, Projectors and HDTV
- Easily connect your PC to a HDTV, Projector and CRT Displays

### Features

- Supports hot plugging of DVI display devices
- Compliant with DVI DDWG Standards
- High speed digital transmission rate of up to 4.95 Gbits/sec
- Compatible with PC and Mac computer systems
- DVI-D Single Link Display Cable supports digital displays only

**Technical Specifications**

Warranty	Lifetime
Industry Standards	DVI DDWG Standard
Connector A	1 - DVI-D (19 pin) Male
Connector B	1 - DVI-D (25 pin) Female
Color	Black
Wire Gauge	28 AWG
Cable Length	10 ft [3 m]
Shipping (Package) Weight	0.7 lb [0.3 kg]
Included in Package	10 ft DVI-D Single Link Monitor Extension Cable - M/F

**Certifications, Reports and Compatibility**

