

15 ft DVI-D Single Link Monitor Extension Cable - M/F

StarTech ID: *DVIDSMF15*



This 15ft single-link DVI-D extension cable offers a high quality connection that allows you to get the most out of your high-end digital video card and flat-panel digital LCD monitor.

With DVI-D technology, no digital-to-analog conversion is necessary, so the signal is delivered faster and stronger than a standard monitor cable signal. The plug and play-compatible, all-digital connection provided by this DVI-D extension cable is also ideal for connecting laptop computers to digital projectors for crystal-clear presentations.

By interfacing two digital signals directly, you'll experience faster, higher-quality images. This single-link cable works with virtually any DVI digital flat panel LCD monitor and allows high-speed DVI video data transmissions of up to 4.95 Gbps.

Applications and Solutions

- Compatible with Flat Panel Displays, Digital CRT Displays, Projectors and HDTV
- Ideal solution for entry-level servers, network-attached storage and complex storage systems

Features

- Compatible with PC and Mac computer systems
- Compliant with DVI DDWG Standards
- DVI-D Single Link Display Cable supports digital displays only
- High speed digital transmission rate of up to 4.95 Gbits/sec
- Supports hot plugging of DVI display devices

Technical Specifications

- Warranty: Lifetime warranty
- Color: Black
- Carton Quantity: 25
- Shipping (Package) Weight: 0.97 lb [0.44 kg]
- Cable Length: 15 ft [4.57 m]
- Connector A: 1 - 19 pin DVI-D (Single Link) Male
- Connector B: 1 - 19 pin DVI-D (Single Link) Female
- Industry Standards: DVI DDWG Standard
- Wire Gauge: 28 AWG

