

## 15 ft DVI-D Single Link Digital Video Monitor Cable - M/M

StarTech ID: DVIDSMM15



This 15ft single-link DVI-D display cable offers a high quality connection that allows you to get the most out of your high-end digital video card and flat-panel digital LCD monitor.

With DVI-D technology, no digital-to-analog conversion is necessary, so the signal is delivered faster and stronger than a standard monitor cable signal. The plug and play-compatible, all-digital connection is also ideal for connecting laptop computers to digital projectors for crystal-clear presentations.

By interfacing two digital signals directly, you'll experience faster, higher-quality images. This single-link cable works with virtually any DVI digital flat panel LCD monitor and allows high-speed DVI video data transmissions of up to 4.95 Gbps.

### Applications and Solutions

- Compatible with Flat Panel Displays, Digital CRT Displays, Projectors and HDTV
- Easily connect your PC to a HDTV, Projector and CRT Displays

## Features

- Compatible with PC and Mac computer systems
- Compliant with DVI DDWG Standards
- DVI-D Single Link Display Cable supports digital displays only
- High speed digital transmission rate of up to 4.95 Gbits/sec
- Supports hot plugging of DVI display devices

## Technical Specifications

- Warranty: Lifetime warranty
- Color: Black
- Carton Quantity: 25
- Shipping (Package) Weight: 1.06 lb [0.48 kg]
- Cable Length: 15 ft [4.57 m]
- Connector A: 1 - 19 pin DVI-D (Single Link) Male
- Connector B: 1 - 19 pin DVI-D (Single Link) Male
- Industry Standards: DVI DDWG Standard
- Wire Gauge: 28 AWG

