

## 20 ft DVI-D Single Link Cable - M/M

StarTech ID: *DVIDSMM20*



The DVIDSMM20 20-foot DVI-D single-link cable features two male DVI digital (single link) connectors and offers a high quality connection which allows you to get the most out of your high-end digital video card and flat-panel digital LCD monitor.

With DVI-D technology, no digital-to-analog conversion is necessary, so the signal is delivered faster and stronger than a standard monitor cable signal. The plug and play-compatible, all-digital connection is also ideal for connecting laptop computers to digital projectors for crystal-clear presentations.

By interfacing two digital signals directly, you'll experience faster, higher-quality images. This single-link cable works with virtually any DVI digital flat panel LCD monitor and allows high-speed DVI video data transmissions of up to 4.95 Gbps.

### Applications

- Ideal solution for entry-level servers, network-attached storage and complex storage systems
- Easily connect your PC to a HDTV, Projector and CRT Displays
- Compatible with PC and Mac® computer systems
- Compatible with Flat Panel Displays, Digital CRT Displays, Projectors and HDTV

### Features

- High speed digital transmission rate of up to 4.95 Gbits/sec
- Compliant with DVI DDWG Standards
- Supports hot plugging of DVI display devices
- Ferrite core eliminates EMI interference

## Technical Specifications

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Type	PVC - Polyvinyl Chloride
Cable Shield Type	Aluminum-Mylar Foil with Braid
Industry Standards	DVI DDWG Standard
Connector A	1 - DVI-D (19 pin) Male
Connector B	1 - DVI-D (19 pin) Male
Color	Black
Wire Gauge	28 AWG
Cable Length	20 ft [6.1 m]
Shipping (Package) Weight	1.3 lb [0.6 kg]
Included in Package	1 - 20ft DVI-D Single Link Cable - M/M

## Certifications, Reports and Compatibility

