

HDTV DVI Repeater/Extender HDCP compliant

StarTech ID: *DVIHDCPEXT*



Don't be held back by DVI cable limitations - now, you can extend your DVI connection by 12m (24m total extension), while enjoying an astounding 1080i or 1600x1200(UXGA)resolution.

Features

- Corrects signal error and extends DVI transmission by 12 meters without degradation
- HDCP 1.1 compliant and backwards compliant with HDCP 1.0
- Plug and Play, easy to install
- DDC pass through ensures proper recognition of the connected display
- Cascadable up to three levels to achieve maximum transmission distance of 72 metres

Technical Specifications

Warranty	2 Years
Ports	1
Cabling	DVI
Connector Type(s)	1 - DVI-D (25 pin) Female
Maximum Analog Resolutions	1080p (HDTV) / 1600x1200 (PC)
General Specifications	DVI-D dual link female connector
Color	Black
Enclosure Type	Aluminum
Product Length	4.1 in [105 mm]
Product Width	3 in [76 mm]
Product Height	1.2 in [30 mm]
Product Weight	0 lb [0 kg]
LED Indicators	1 - Power LED (red)
Power Adapter Included	Yes
Center Tip Polarity	Positive
Shipping (Package) Weight	1.1 lb [0.5 kg]
Included in Package	1 - HDCP DVI Extender
Included in Package	1 - Power Adapter
Included in Package	1 - User Manual

Certifications, Reports and Compatibility

