

## 10 ft DVI-I Dual Link Digital Analog Monitor Extension Cable - M/F

StarTech ID: DVIIDMF15



This 15ft DVH Dual Link DVH Extension Cable features a male DVH (dual link) connector and a female DVH (dual link) connector, allowing you to extend an existing digital or analog video connection by 15ft.

Supporting hot-pluggable DVI display connections, the DVI-I extension cable provides an impressive 9.9Gbps video bandwidth to deliver crystal clear images and video, suitable for virtually any application.

Backed by Lifetime Warranty, StarTech.com's 15ft DVH Dual Link Digital/Analog Extension Cable is designed and constructed to provide maximum durability and video quality.

### Applications

- Compatible with Flat Panel Displays, Digital CRT Displays, Projectors and HDTV
- Easily connect your PC to a HDTV, Projector and CRT Displays
- Extends the distance of your DVI-I digital video device

### Features

- Supports hot plugging of DVI display devices
- Compliant with DVI DDWG Standards
- High speed digital transmission rate of up to 9.9 Gbits/sec
- Dual link digital signalling allows high speed digital data transmission
- Compatible with PC and Mac computer systems
- DVH Dual Link Display Cable supports both analog and digital displays

## Technical Specifications

Warranty	Lifetime
Industry Standards	DVI DDWG Standard
Connector A	1 - DVI-I (29 pin) Female
Connector B	1 - DVI-I (29 pin) Male
Maximum Data Transfer Rate	9.9 Gbits/sec
Color	Black
Cable Length	15 ft [4.6 m]
Product Weight	25.3 oz [716 g]
Shipping (Package) Weight	1.6 lb [0.7 kg]

## Certifications, Reports and Compatibility

