

## 15 ft DVI-I Dual Link Digital Analog Monitor Cable M/M

StarTech ID: DVIIDMM15



This 15ft DVI-I dual link digital/analog video cable features two male DVI-I connectors with support for high speed data transmissions of up to 9.9Gbps between DVI devices. This cable provides a reliable, high quality connection to devices such as flat panel displays, HDTVs, Blu-Ray players, DVD players and more.

Expertly designed and constructed of only top quality materials, this DVI-I dual link cable is backed by StarTech.com's Lifetime Warranty.

### Applications and Solutions

- Compatible with Flat Panel Displays, Digital CRT Displays, Projectors and HDTV
- Easily connect your PC to a HDTV, Projector and CRT Displays

## Features

- Compatible with PC and Mac computer systems
- Compliant with DVI DDWG Standards
- Dual link digital signalling allows high speed digital data transmission
- DVI-I Dual Link Display Cable supports both analog and digital displays
- High speed digital transmission rate of up to 9.9 Gbits/sec
- Supports hot plugging of DVI display devices

## Technical Specifications

- Warranty: Lifetime warranty
- Color: Black
- Carton Quantity: 25
- Shipping (Package) Weight: 1 lb [0.45 kg]
- Cable Length: 15 ft [4.57 m]
- Connector A: 1 - 29 pin DVI-I (Dual Link) Male
- Connector B: 1 - 29 pin DVI-I (Dual Link) Male
- Maximum Data Transfer Rate: 9.9 Gbits/sec
- Industry Standards: DVI DDWG Standard
- Wire Gauge: 28 AWG

