

15 ft DVI-I Dual Link Digital Analog Monitor Cable M/M

StarTech ID: *DVIIDMM15*



This 15ft DVI-I dual link digital/analog video cable features two male DVI-I connectors with support for high speed data transmissions of up to 9.9Gbps between DVI devices. This cable provides a reliable, high quality connection to devices such as flat panel displays, HDTVs, Blu-Ray players, DVD players and more.

Expertly designed and constructed of only top quality materials, this DVI-I dual link cable is backed by StarTech.com's Lifetime Warranty.

Applications

- Compatible with Flat Panel Displays, Digital CRT Displays, Projectors and HDTV
- Easily connect your PC to a HDTV, Projector and CRT Displays

Features

- Supports hot plugging of DVI display devices
- Compliant with DVI DDWG Standards
- High speed digital transmission rate of up to 9.9 Gbits/sec
- Dual link digital signalling allows high speed digital data transmission
- Compatible with PC and Mac computer systems
- DVH Dual Link Display Cable supports both analog and digital displays

Technical Specifications

Warranty	Lifetime
Industry Standards	DVI DDWG Standard
Connector A	1 - DVI-I (29 pin) Male
Connector B	1 - DVI-I (29 pin) Male
Maximum Data Transfer Rate	9.9 Gbits/sec
Color	Black
Wire Gauge	28 AWG
Cable Length	15 ft [4.6 m]
Shipping (Package) Weight	1 lb [0.5 kg]
Included in Package	15 ft DVI-I Dual Link Digital Analog Monitor Cable M/M

Certifications, Reports and Compatibility

