

6 ft DVI-I Dual Link Digital Analog Monitor Cable M/M

StarTech ID: *DVIIDMM6*



This 6ft DVH dual link digital/analog video cable features two male DVH connectors with support for high speed data transmissions of up to 9.9Gbps between DVI devices. The cable provides a reliable, high quality connection to devices such as flat panel displays, HDTVs, Blu-Ray players, DVD players and more.

Expertly designed and constructed of only top quality materials, this DVH dual link video cable is backed by StarTech.com's Lifetime Warranty.

Applications

- Compatible with Flat Panel Displays, Digital CRT Displays, Projectors and HDTV
- Connect your PC to a HDTV, Projector and CRT Displays
- Compatible with PC and Mac® computer systems
- Compatible with PC and Mac® computer systems
- DVH Dual Link Display Cable supports both analog and digital displays
- DVH Dual Link Display Cable supports both analog and digital displays

Features

- High speed digital transmission rate of up to 9.9 Gbits/sec
- Compliant with DVI DDWG Standards
- Supports hot plugging of DVI display devices
- Ferrite core eliminates EMI interference

Technical Specifications

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Type	PVC - Polyvinyl Chloride
Cable Shield Type	Aluminum-Mylar Foil with Braid
Industry Standards	DVI DDWG Standard
Connector A	1 - DVH (29 pin) Male
Connector B	1 - DVH (29 pin) Male
Maximum Data Transfer Rate	9.9 Gbits/sec
Color	Black
Wire Gauge	28 AWG
Cable Length	6 ft [1.8 m]
Product Weight	0.8 lb [0.4 kg]
Shipping (Package) Weight	0.8 lb [0.4 kg]
Included in Package	1 - 6 ft DVH Dual Link Digital Analog Monitor Cable M/M

Certifications, Reports and Compatibility

