

15 ft DVI-I Single Link Digital Analog Monitor Cable M/M

StarTech ID: *DVIISMM15*



This 15 ft DVH Single Link Monitor Cable features two DVI-I male connectors, providing a high quality digital/analog connection between DVH devices such as digital and flat panel displays, projectors and CRT monitors, with support for high speed video data transmission of up to 4.5Gbps.

Expertly designed and constructed of only top quality materials, this high quality DVI video cable is backed by StarTech.com's Lifetime Warranty.

Applications

- Compatible with Flat Panel Displays, Digital CRT Displays, Projectors and HDTV
- Easily connect your PC to a HDTV, Projector and CRT Displays

Features

- Supports hot plugging of DVI display devices
- Compliant with DVI DDWG Standards
- High speed digital transmission rate of up to 4.95 Gbits/sec
- Single link digital signalling allows high speed digital data transmission
- Compatible with PC and Mac computer systems
- DVH Single Link Display Cable supports both analog and digital displays

Technical Specifications

Warranty	Lifetime
Industry Standards	DVI DDWG Standard
Connector A	1 - DVI (23 pin) Male
Connector B	1 - DVI (23 pin) Male
Maximum Data Transfer Rate	4.95 Gbits/sec
Color	Black
Wire Gauge	28 AWG
Cable Length	15 ft [4.6 m]
Shipping (Package) Weight	1.5 lb [0.7 kg]
Included in Package	1 - 15 ft DVI Single Link Digital Analog Monitor Cable M/M

Certifications, Reports and Compatibility

