

2 Port ExpressCard Laptop 1394a Firewire Adapter Card
StarTech ID: EC13942



This 2 Port ExpressCard Laptop 1394a Firewire Adapter Card provides a stable platform for virtually any FireWire 400 device connection.

Ensuring seamless operation with peripherals connected through FireWire 400, the ExpressCard 1394a FireWire Adapter supports data transfer rates at up to 400Mbps - perfect for connecting FireWire-capable multimedia devices, editing multimedia content or simply transferring large volumes of data from a computer to FireWire-connected external storage.

Applications and Solutions

- Add a high speed FireWire port to a laptop without any FireWire ports
- Connect a digital camera to a laptop with an ExpressCard slot to download photos or video
- Connect a high speed external hard drive to an ExpressCard enabled system

Features

- Two 6-pin FireWire ports, each with transfer rates up to 400 Mbps
- Compliant with IEEE 1394-1995, 1394a-2000 and OHCI 1.1 standards
- Fits in 34mm and 54mm ExpressCard slots
- Plug-and-Play and hot-swap compatible

Technical Specifications

- Warranty: Lifetime
- Interface: FireWire 400 (1394a)
- Bus Type: ExpressCard
- Card Type: 34mm ExpressCard
- Chipset ID: TI XIO2200A
- Product Height: 2.6 in [66 mm]
- Product Length: 9.65 in [245 mm]
- Maximum Data Transfer Rate: 400 Mbps
- Ports: 2
- OS Compatibility: Windows 2000/ XP(32/64bit)/ 2003(32/64bit)/ Vista(32/64bit)/ 7(32/64bit), and Linux
- Output Current: 1000+ mA
- Carton Quantity: 40
- Shipping (Package) Weight: 0.4 lb [0.18 kg]
- Product Weight: 3.53 oz [100 g]
- Product Width: 5.91 in [150 mm]
- System and Cable Requirements: One available ExpressCard Slot

