

2 Port ExpressCard eSATA Controller Adapter Card

StarTech ID: ECESATA22



This 2 Port eSATA ExpressCard adapter lets laptop users experience the high performance capability of eSATA storage for data transfer rates of up to 3Gbps, as well as port multiplier capability with command-based switching for connecting multiple external hard drives to a host PC or Mac notebook through one eSATA connection.

Using a native PCI Express single chipset, the eSATA controller provides enhanced compatibility, reliability and performance for your external storage needs.

Applications and Solutions

- Add eSATA connectivity to a laptop to connect with high speed external storage devices
- Upgrade from connecting external storage devices with USB 2.0 to faster eSATA

Features

- Two external SATA (eSATA) ports
- Supports FIS and Command-based Port Multiplier technology
- Fits in 34mm and 54mm ExpressCard slots
- Compliant with Serial ATA 2.5 specifications with transfer rates up to 3.0 Gbps
- Hot-Swap compatible
- Uses native PCI Express single chipset

Technical Specifications

- Warranty: Lifetime warranty
- Bus Type: ExpressCard
- Number of Ports: 2
- Port Multiplier Support: Yes
- Carton Quantity: 50
- Shipping (Package) Weight: 0.2 lb [0.09 kg]
- Bus Type: ExpressCard
- Chipset: Silicon Image - Sil3132
- OS Compatibility: Windows 2000/ XP(32/64bit)/ 2003(32/64bit)/ Vista(32/64bit)/ 7(32/64bit), Mac OS X 10.4.9, 10.4.10 and 10.5.1. and Linux

