

## 2 Port ExpressCard eSATA Controller Adapter Card

StarTech ID: ECESATA22



This 2 Port eSATA ExpressCard adapter lets laptop users experience the high performance capability of eSATA storage for data transfer rates of up to 3Gbps, as well as port multiplier capability with command-based switching for connecting multiple external hard drives to a host PC or Mac notebook through one eSATA connection.

Using a native PCI Express single chipset, the eSATA controller provides enhanced compatibility, reliability and performance for your external storage needs.

### Applications

- Add eSATA connectivity to a laptop to connect with high speed external storage devices
- Upgrade from connecting external storage devices with USB 2.0 to faster eSATA

### Features

- Two external SATA (eSATA) ports
- Supports FIS and Command-based Port Multiplier technology
- Fits in 34mm and 54mm ExpressCard slots
- Compliant with Serial ATA 2.5 specifications with transfer rates up to 3.0 Gbps
- Hot-Swap compatible
- Uses native PCI Express single chipset

## Technical Specifications

Warranty	Lifetime
Ports	2
Interface	eSATA
Bus Type	ExpressCard
Card Type	34mm ExpressCard
Chipset ID	Silicon Image - Si3132
Connector Type(s)	1 - ExpressCard (34mm)
External Ports	2 - eSATA (7 pin; Data) Plug
Type and Rate	SATA II (3 Gbps)
Port Multiplier	Yes
RAID	No
OS Compatibility	Windows 2000/ XP(32/64bit)/ 2003(32/64bit)/ Vista(32/64bit)/ 7(32/64bit), Mac OS X 10.4.9, 10.4.10 and 10.5.1. and Linux
Product Length	4.4 in [112 mm]
Product Width	1.3 in [34 mm]
Product Height	0.8 in [21 mm]
Product Weight	1.4 oz [40 g]
Shipping (Package) Weight	0.2 lb [0.1 kg]
Included in Package	1 - eSATA ExpressCard Controller Card
Included in Package	1 - Driver CD
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

