

2 Port ExpressCard SuperSpeed USB 3.0 Card Adapter

StarTech ID: ECUSB3S2



Providing speeds up to 10x faster than that of USB 2.0, this ExpressCard USB 3.0 card enables you to access your data and transfer files much faster than USB 2.0, by adding two USB 3.0 ports to your ExpressCard capable laptop.

Featuring a native NEC PCI Express host controller chipset, the new SuperSpeed USB supports transfer rates up to 5Gbps, while still providing connectivity and support for older USB 2.0 (480Mbps) and 1.1 (12Mbps) devices.

Designed to provide reliable SuperSpeed USB 3.0 connections, this ExpressCard adapter is backed by StarTech.com's lifetime warranty and free lifetime technical support.

Applications and Solutions

- Update an older laptop with USB 3.0 connectivity
- Expand a system's USB capabilities with two additional USB ports
- Connect additional external hard drives, CD/DVD drives, MP3 players, printers, scanners, webcams, game controllers, digital cameras, etc. to a computer system

Features

- Fully compliant with USB 3.0 rev 1.0 specifications and Intel xHCI rev 0.96 specifications, with transfer rates up to 5Gbps
- Backwards compatible with USB 2.0 and 1.1/1.0 devices
- Provides up to 900mA of power per port, with additional power adapter
- Supports Control/Bulk/Interrupt/Isochronous USB transfer modes
- Support for up to 127 USB devices per port (requires additional USB hubs)
- Compliant with ExpressCard 1.0 specifications
- Plug-and-Play and hot-swap compliant
- Fits in 34mm and 54mm ExpressCard slots

Technical Specifications

- Warranty: Lifetime warranty
- Bus Type: ExpressCard
- Product Height: 0.83 in [21 mm]
- Humidity: 0~85% RH
- Product Length: 4.53 in [115 mm]
- Operating Temperature: -0°C to 50°C (32°F to 122°F)
- Carton Quantity: 80
- Storage Temperature: -20°C to 60°C (-4°F to 140°F)
- Shipping (Package) Weight: 0.27 lb [0.12 kg]
- Product Weight: 1.59 oz [45 g]
- Product Width: 1.34 in [34 mm]
- Chipset ID: NEC Electronics - μ PD720200
- Card Type: 34mm ExpressCard
- Number of Ports: 2
- External Ports: 2 - USB A 3.0 Female
- Type and Rate: USB 3.0 - 5 Gbit/s
- Power Adapter Included: No
- Output Voltage: 5 DC
- Output Current: 2000mA
- Center Tip Polarity: Positive
- Plug Type: H

- OS Compatibility: Windows XP(32/64bit)/ 2003(32/64bit)/ Vista(32/64bit)/ 7(32/64bit)

