

3 ft eSATA and USB A to Power eSATA Cable - M/M

StarTech ID: ESATAUSBMM3



This eSATA and USB A Male to Power eSATA Cable provides a 3ft connection between an external drive enclosure equipped with a power eSATA port and the eSATA and USB port on a PC/Notebook, providing both power (through USB) and data (through SATA) using a single cable.

Expertly designed and constructed of only top quality materials, the 3ft eSATA and USB A Male to Power eSATA Male cable is backed by StarTech.com's Lifetime Warranty.

Applications

- Connect your Powered eSATA device to your PC or Notebook even if you do not have a Powered eSATA port

Features

- Combo eSATA + USB connection
- Compliant with Serial ATA III Specifications

Technical Specifications

Warranty	Lifetime
Cable Jacket Type	PVC - Polyvinyl Chloride
Connector A	1 - Power eSATA (11 pin; eSATA/USB; 5/12V) Receptacle
Connector B	1 - eSATA (7 pin; Data) Receptacle
Connector B	1 - USB A (4 pin) Male
Color	Black
Cable Length	3 ft [0.9 m]
Operating Temperature	-205/8/2012eg;C to 505/8/2012eg;C (-45/8/2012eg;F to 1225/8/2012eg;F)
Storage Temperature	-205/8/2012eg;C to 605/8/2012eg;C (-45/8/2012eg;F to 1405/8/2012eg;F)
Humidity	60~75% RH
Shipping (Package) Weight	0.2 lb [0.1 kg]
Included in Package	1 - 3ft USB and ESATA to Power eSATA

Certifications, Reports and Compatibility

