

40x10mm Replacement Dual Ball Bearing Computer Case Fan w/ LP4

StarTech ID: FAN4X1LP4



This 40mmx10mm PC computer cooling fan is a perfect addition or replacement PC fan for maintaining suitable operating temperatures within your computer case.

The PC fan can be powered through a simple LP4 connection to the PC power supply and offers a dual ball bearing design to ensure quiet, dependable operation.

Applications

- Replace a noisy or failed computer case fan
- Install into a computer chassis to increase air flow and cooling

Features

- Dual ball bearing design
- Inline LP4 power connectors

Technical Specifications

Warranty	2 Years
Number of Conductors	2
Fan Bearing Type	Ball Bearing
Connector Type(s)	1 - LP4 (4 pin; Molex Large Drive Power) Female
Connector Type(s)	1 - LP4 (4 pin; Molex Large Drive Power) Male
Fan RPM	5000
Air Flow Rate	5.22 CFM
Noise Level	23 dBA
Color	Black
Enclosure Type	Plastic
Product Length	1.6 in [40 mm]
Product Width	0.4 in [10 mm]
Product Height	1.6 in [40 mm]
Product Weight	0.9 oz [25 g]
Input Voltage	12 DC
Operating Temperature	-10 to 80
Shipping (Package) Weight	0.1 lb [0 kg]
Included in Package	1 - 4 cm Case Fan

Certifications, Reports and Compatibility

