

40x20mm Replacement Dual Ball Bearing Computer Case Fan w/ LP4

StarTech ID: FAN4X2LP4



This 40x20mm PC computer cooling fan is a perfect addition or replacement PC fan for maintaining suitable operating temperatures within your computer case.

The PC fan can be powered through a simple LP4 connection to the PC power supply and offers a dual ball bearing design to ensure quiet, dependable operation.

Applications and Solutions

- Install in your workstation to keep your hardware cool
- Replaces a non-functional or a noisy fan in a PC

Features

- Dual Ball Bearings in the cooling fan provides increased airflow, reliability and longer life

Technical Specifications

- Warranty: 1 Year warranty
- Air Flow Rate: 4.65
- Color: Black
- Connector Types: 1 - LP4 Male
- Connector Types: 1 - LP4 Female
- Enclosure Type: Plastic
- Fan Bearing Type: Ball Bearing
- Product Height: 1.57 in [40 mm]
- Input Voltage: 12 DC
- Product Length: 1.57 in [40 mm]
- Noise Level: 23
- Number of Conductors: 2
- Operating Temperature: -10 to 80
- Carton Quantity: 240
- RPM: 5500
- Shipping (Package) Weight: 0.09 lb [0.04 kg]
- Product Weight: 0.88 oz [25 g]
- Product Width: 0.79 in [20 mm]

