

## 40x20mm Replacement Dual Ball Bearing Computer Case Fan w/ LP4

StarTech ID: FAN4X2LP4



This 40x20mm PC computer cooling fan is a perfect addition or replacement PC fan for maintaining suitable operating temperatures within your computer case.

The PC fan can be powered through a simple LP4 connection to the PC power supply and offers a dual ball bearing design to ensure quiet, dependable operation.

### Applications

- Install in your workstation to keep your hardware cool
- Replaces a non-functional or a noisy fan in a PC

### Features

- Dual Ball Bearings in the cooling fan provides increased airflow, reliability and longer life

### Technical Specifications

Warranty	2 Years
Number of Conductors	2
Fan Bearing Type	Ball Bearing
Connector Type(s)	1 - LP4 (4 pin; Molex Large Drive Power) Female
Connector Type(s)	1 - LP4 (4 pin; Molex Large Drive Power) Male
Fan RPM	5500
Air Flow Rate	4.65 CFM
Noise Level	23 dBA
Color	Black
Enclosure Type	Plastic
Product Length	1.6 in [40 mm]
Product Width	0.8 in [20 mm]
Product Height	1.6 in [40 mm]
Product Weight	0.9 oz [25 g]
Input Voltage	12 DC
Operating Temperature	-10 to 80
Shipping (Package) Weight	0.1 lb [0 kg]
Included in Package	1 - 40mm Ball Bearing Fan

### Certifications, Reports and Compatibility

