

Intel Socket 775 Heatsink with Fan.

StarTech ID: FAN775



FAN775 is built to cool the power hungry 775 Intel Processor. The extruded aluminum uses aluminum alloy material and the radial fin design directs hot air away from the CPU. Comes complete with thermal transfer compound for quick, professional quality installation.

Applications

- Intel Socket 775, P4 (up to 3.8 GHz)

Features

- Improves cooling capacity of the CPU cooler by thermally bonding the CPU to the heatsink (thermal transfer compound included)
- Large aluminum heatsink provides efficient heat dissipation
- StarTech.com's CPU cooler heatsink / fan combination delivers better cooling performance and keeps your system stable
- Quiet and Stylish Ball Bearing Fan!

Technical Specifications

Warranty	2 Years
Number of Conductors	4 Pin Connector
Fan Bearing Type	Ball Bearing
Connector Type(s)	1 - Molex Fan (3 pin; TX3) Female
Fan RPM	1500 ~ 3500
Air Flow Rate	26.97 ~ 52.4 CFM
Noise Level	27 dBA
General Specifications	0.23° C/W
General Specifications	0.85 Lbs
General Specifications	3.86 x 3.86 x 3.50 in.
General Specifications	92 x 92 x 32 mm
General Specifications	Supports up to Intel P4 3.8 GHz
Color	Blue
Shipping (Package) Weight	1.3 lb [0.6 kg]

Certifications, Reports and Compatibility

