

1U Low Profile 70mm Socket 775 CPU Cooler Fan w/ Heatsink & TX3

StarTech ID: FAN7751U



This Low Profile 70mm Socket 775 CPU Cooler Fan is designed specifically for use with processors in rack-mounted and low profile mini systems.

Suitable for Dual Core and high-speed Pentium 4 processors, the low profile Socket 775 CPU Fan is compatible with Intel Socket LGA775 P4 (up to 3.8 GHz) and Dual Core processors and features a dual ball-bearing 70mm fan for exceptional cooling and extended service life.

The CPU fan also features a built-on all-copper base skive fin heatsink and includes our thermal CPU paste that helps the cooling capability of the CPU cooler by thermally bonding the CPU to the heatsink for greater dissipation.

Powered through a simple TX3 connection to the computer power supply, the Socket 775 CPU cooler is backed by 2-year warranty.

Applications

- Building a Socket 775-based 1U rack mount server
- Replace the stock/OEM cooler for a Socket 775 system

Features

- Dual ball-bearing 70mm cooling fan
- All copper base, skive-fin heatsink

Technical Specifications

Warranty	2 Years
Fan Dimensions	70 x 70 x 10 mm (2.76 x 2.76 x .39 in.)
Fan Bearing Type	Ball Bearing
Heatsink Dimensions	3.58 x 3.58 x .55 in. (91 x 91 x 14 mm)
Connector Type(s)	1 - Molex Fan (3 pin; TX3) Female
Fan RPM	4500 +/- 10% RPM
Air Flow Rate	30.79 CFM
Noise Level	< 39 dBA
MTBF	50,000 Hours
Color	Black
Product Length	3.7 in [95 mm]
Product Width	3.7 in [95 mm]
Product Height	0.9 in [24 mm]
Product Weight	17.4 oz [493 g]
Input Voltage	12 DC
Shipping (Package) Weight	1.3 lb [0.6 kg]
Included in Package	1 - Heatsink Fan assembly
Included in Package	1 - Backing Plate
Included in Package	1 - Thermal Compound
Included in Package	4 - Mounting Screw/Nut
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

