

Copper Pentium 4 Heatsink with Fan

StarTech ID: FANP4CU



Make sure your hard-working Pentium 4 CPU stays cool with StarTech.com's FANP4CU. To get the most out of your P4 you've got to keep the temperature down, so we've designed the FANP4CU with an extra-large, all-copper heatsink that efficiently pulls the heat off your CPU and delivers maximum cooling. And the FANP4CU looks as good as it performs: the gold-colored ball-bearing fan and cool black design looks great inside any case. Get maximum performance from your P4 with maximum cooling from StarTech.com.

Applications

- Intel P4 3.2 GHz and higher processors

Features

- Copper heatsink and ball bearing fan combination delivers better cooling performance and keeps your system stable
- Designed to work with Intel P4 Processors
- 100% copper heatsink construction provides efficient heat dissipation
- Easy installation on your motherboard

Technical Specifications

Warranty	Lifetime
Fan Bearing Type	Ball Bearing
Connector Type(s)	1 - Molex Fan (3 pin; TX3) Female
Fan RPM	3500
Air Flow Rate	27.9 CFM
General Specifications	Intel P4 3.2 GHz and higher
General Specifications	<34 dBA
General Specifications	100% copper
General Specifications	2.1 Watts (0.18A)
General Specifications	27.9 CFM
General Specifications	345g
General Specifications	3500 RPM
General Specifications	70 x 70 x 15 mm
General Specifications	86.6 x 70 x 45 mm
General Specifications	CE
Color	Black
Product Length	3.3 in [8.5 cm]
Product Width	2.8 in [7 cm]
Product Height	2 in [5.2 cm]
Product Weight	12.2 oz [345 g]
Shipping (Package) Weight	1.2 lb [0.6 kg]

Certifications, Reports and Compatibility

