

6 ft USB to Parallel Printer Adapter - M/M

StarTech ID: ICUSB1284



The ICUSB1284 6 ft USB to Parallel Printer Adapter - M/M allows USB capable PCs to print to any standard parallel printer, converting a USB port into a Centronics (male) connector for direct connection to a parallel printer.

The USB interface provides a much faster data transfer rate than standard parallel ports, thereby reducing the time spent waiting for a print job or data transfer to be sent.

A portable, space-saving solution, the USB to Parallel Printer Adapter is self-powered and provides Plug and Play installation on Windows® based, USB-compliant computers.

Backed by a StarTech.com lifetime warranty and free lifetime technical support.

Applications

- Allows you to quickly add a parallel port to your Windows® computer

Features

- High speed bi-directional parallel port compliant to IEEE-1284 industry standard
- Low power consumption as it draws power from the USB connection
- Fully Plug & Play for easy installation
- No IRQ required for installation

Technical Specifications

Warranty	2 Years
Chipset ID	Prolific - PL-2305
Ports	1
Bus Type	USB 2.0
Connector Type(s)	1 - Centronics (36 pin) Male
Connector Type(s)	1 - USB A (4 pin) Male
OS Compatibility	Windows® 8 (32/64bit), 7 (32/64), Vista(32/64), XP(32/64), 2000, ME, 98SE Windows® Server 2008 R2
Enclosure Type	Plastic
Cable Length	70.9 in [180 cm]
Product Length	6.1 ft [1.9 m]
Product Weight	3.9 oz [110 g]
Power Adapter Included	Self Powered
Power Consumption	0.9W
Operating Temperature	55/21/2012eg;C to 405/21/2012eg;C (415/21/2012eg;F to 1405/21/2012eg;F)
Storage Temperature	-205/21/2012eg;C to 705/21/2012eg;C (-45/21/2012eg;F to 1585/21/2012eg;F)
Humidity	0~80% RH non-condensing
Shipping (Package) Weight	0.3 lb [0.2 kg]
Included in Package	1 - CONVERTER CABLE
Included in Package	1 - DRIVER DISKETTE (5.25" DISKETTE)

Certifications, Reports and Compatibility

