

6 ft USB to DB25 Parallel Printer Adapter Cable - M/F

StarTech ID: ICUSB1284D25



The ICUSB1284D25 6 ft USB to DB25 Parallel Printer Adapter Cable turns an available USB port on a host PC into a DB25 Female Parallel port - allowing you to connect a DB25 printer to the computer as if the necessary parallel port was built-on.

A cost-effective and reliable solution, the USB to DB25 adapter saves the expense of replacing a parallel printer for the sake of USB capability.

Backed by a StarTech.com 2-year warranty and free lifetime technical support .

Applications

- Allows you to quickly add a parallel port to your computer for use with printers with DB25 connectors
- Ideal solution for notebooks or desktops without a Parallel port

Features

- Fully Plug & Play for easy installation
- USB bus-powered operation, no external power adapter required
- Eliminates the need for manual or automatic parallel switch boxes

Technical Specifications

Warranty	2 Years
Chipset ID	Prolific - PL-2305
Ports	1
Bus Type	USB 2.0
Connector Type(s)	1 - DB-25 (25 pin; D-Sub) Female
Connector Type(s)	1 - USB A (4 pin) Male
Maximum Data Transfer Rate	1.5Mbps
OS Compatibility	Windows® 8 (32/64bit), 7 (32/64), Vista(32/64), XP(32/64), 2000, 98SE Mac OS 10.4 and up (Tested up to 10.8)
Product Length	6.1 ft [1.9 m]
Product Weight	3.5 oz [100 g]
Operating Temperature	5°C to 40°C (41°F to 140°F)
Storage Temperature	-20°C to 70°C (-4°F to 158°F)
Humidity	0~80% RH non-condensing
Shipping (Package) Weight	0.3 lb [0.1 kg]
Included in Package	1 - USB to Parallel Adapter Cable
Included in Package	1 - Driver CD
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility



