

## 24in Internal USB Motherboard Header to Parallel Adapter

StarTech ID: ICUSB1284INT



The ICUSB1284INT Internal USB Motherboard Header to Parallel Adapter lets you add a parallel port to any standard or low-profile/half-height desktop system that is equipped with an available USB motherboard header, offering data transfer rates up to 1.5Mbps.

Unlike standard USB to parallel cables, this cable is designed for use inside the PC case, affording an entirely internal solution with no mess or extra adapters needed.

This compact and simple USB adapter offers a cost-effective solution that bridges the compatibility gap between modern computers and legacy parallel peripherals.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Applications

- Quickly add a parallel port to your computer for use with printers utilizing DB25 connectors
- Perfect for system builders looking to add legacy functionality to newer motherboards that lack an integrated parallel port

## Features

- Fully automatic, high speed bi-directional parallel port
- 512 Bytes dynamically allocated unified data buffer for upstream and downstream data transfer
- Standard profile full-height bracket installed
- Includes optional low profile/half-height bracket
- On-chip transceivers and regulator for USB interface
- Full compliance with IEEE 1284-1994
- Bus-Powered – no separate power supply or battery required
- USB 1.1 compatible

**Technical Specifications**

Warranty	2 Years
Ports	1
Interface	Parallel
Bus Type	Motherboard Header
Card Type	Standard Profile (LP bracket incl.)
Port Style	Integrated on Card
Industry Standards	IEEE 1284
Chipset ID	Prolific - PL-2305
Internal Ports	1 - IDC (10 pin; Motherboard Header) Female
External Ports	1 - DB-25 (25 pin; D-Sub) Female
Maximum Data Transfer Rate	1.5Mbps
OS Compatibility	Windows® 7(32/64bit)/ Server 2008 R2/ Vista(32/64bit)/ XP(32/64bit)/ Server 2003(32/64bit)/ 2000/ Server 2000 Mac OS X (10.6.x) Linux
Microsoft WHQL Certified	Yes
Cable Length	24 in [610 mm]
Product Length	1.6 in [40 mm]
Product Width	2.1 in [53 mm]
Product Height	6.9 in [176 mm]
Product Weight	1.9 oz [55 g]
Operating Temperature	05/23/2012eg;C to 1155/23/2012eg;C (325/23/2012eg;F to 2395/23/2012eg;F)
Storage Temperature	-555/23/2012eg;C to 1505/23/2012eg;C (-675/23/2012eg;F to 3025/23/2012eg;F)
Shipping (Package) Weight	0.3 lb [0.1 kg]
Included in Package	1 - USB header to Parallel Adapter
Included in Package	1 - Low profile bracket
Included in Package	1 - Driver CD
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

