

## 8 Port USB to RS232 Serial DB9 Adapter Hub

StarTech ID: ICUSB2328



This 8 Port USB to RS232 Serial Hub lets you connect up to eight RS232 serial devices to your Mac or PC laptop or desktop computer through a single USB port, as though the computer offered built-on DB9M serial connectors.

The RS232 Serial Hub is compactly designed to preserve valuable workspace, and is bus-powered to eliminate the need for an external power adapter.

A cost-effective solution that bridges the compatibility gap between modern USB-capable computers and legacy RS232 serial peripherals, this dependable USB/RS232 Serial Adapter hub is backed by StarTech.com's Lifetime Warranty.

### Applications and Solutions

- Connect modems, digitizer tablets, mice, bar code scanners, GPS receivers, ISDN terminal adapters, mobile phones, scanners, UPS and POS equipment to your system
- Connect and program LED and Digital signage boards with serial communication ports

## Features

- Adds eight RS232 serial ports using USB
- Bus-powered – requires no external power adapter
- Easy Plug-and-Play installation
- Fully compliant with USB 1.1 specifications and compatible with USB 2.0

## Technical Specifications

- Warranty: Lifetime warranty
- Connector Types: 1 - USB B Male
- Connector Types: 8 - DB9 Male
- Product Height: 1.02 in [26 mm]
- Product Length: 5.91 in [150 mm]
- Maximum Data Transfer Rate: 115000 Kbits/Sec
- Output Current: 1000mA+
- Plug Type: M
- Power Adapter Included: Optional
- Center Tip Polarity: Positive
- Carton Quantity: 20
- Shipping (Package) Weight: 1.86 lb [0.84 kg]
- Product Weight: 30.36 oz [860 g]
- Product Width: 2.62 in [66.5 mm]
- General Specifications: Supports 7,8 Data Bits
- General Specifications: Baud Rate from 300 bps to 921.6Kbps
- Cable Length: 6 feet (1.82 meters)
- Output Voltage: 5 DC
- Chipset ID: FTDI FT232RL
- OS Compatibility: Windows 98SE/ ME/ 2000/ XP(32/64bit)/ Vista(32/64bit)/ 7(32/64bit), Mac OS X, and Linux

