

## 8 Port USB to RS232 Serial DB9 Adapter Hub

StarTech ID: ICUSB2328



The ICUSB2328 8 Port USB to Serial RS232 DB9 Adapter Hub lets you connect up to eight RS232 serial devices to your Mac or PC, laptop or desktop computer through a single USB port, as though the computer offered integrated DB9M serial connectors.

The RS232 Serial Hub is compactly designed to preserve valuable workspace, and is bus-powered to eliminate the need for an external power adapter or wall outlet - a cost-effective solution that bridges the compatibility gap between modern USB-capable computers and legacy RS232 serial peripherals.

Backed by a StarTech.com lifetime warranty and free lifetime technical support.

### Applications

- Connect modems, digitizer tablets, mice, bar code scanners, GPS receivers, ISDN terminal adapters, mobile phones, scanners, UPS and POS equipment to your system
- Connect and program LED and Digital signage boards with serial communication ports

### Features

- Adds eight Straight-Through RS232 serial ports using USB
- Bus-powered – requires no external power adapter
- Easy Plug-and-Play installation
- Fully compliant with USB 1.1 specifications and compatible with USB 2.0

## Technical Specifications

|                            |   |
|----------------------------|---|
| Warranty                   | Lifetime  |
| Ports                      | 8   |
| Bus Type                   | USB 2.0   |
| Port Style                 | External Hub  |
| Chipset ID                 | FTDI - FT232RL  |
| Connector Type(s)          | 1 - USB B (4 pin) Female  |
| External Ports             | 8 - DB-9 (9 pin; D-Sub) Male  |
| Maximum Data Transfer Rate | 115.2 Kbps  |
| Serial Protocol            | RS-232  |
| Max Baud Rate              | 921.6 Kbps  |
| Data Bits                  | 7, 8  |
| OS Compatibility           | Windows® 8 (32/64bit), 7 (32/64), Vista(32/64), XP(32/64), 2000, ME, 98SE<br>Mac OS 10.x (Tested up to 10.8)<br>Linux |
| Cable Length               | 6 ft [1.8 m]  |
| Product Length             | 5.9 in [150 mm]   |
| Product Width              | 2.6 in [66.5 mm]  |
| Product Height             | 1 in [26 mm]  |
| Product Weight             | 30.4 oz [860 g]   |
| Power Adapter Included     | Optional  |
| Output Voltage             | 5 DC  |
| Output Current             | 1A+   |
| Center Tip Polarity        | Positive  |
| Plug Type                  | M   |
| Shipping (Package) Weight  | 1.9 lb [0.8 kg]   |
| Included in Package        | 1 - 8 Port Serial Hub   |
| Included in Package        | 1 - Serial Breakout Cable   |
| Included in Package        | 1 - 6ft USB Cable   |
| Included in Package        | 1 - Driver CD   |
| Included in Package        | 1 - User Manual   |

Certifications, Reports and Compatibility

