

## 4 Port USB to RS-232 Serial DB9 Adapter

StarTech ID: ICUSB232\_4



Got more serial peripherals than you do ports? Don't sweat it, StarTech.com has the solution to your problem with the ICUSB232\_4. It equips your system with four RS-232 serial ports while taking up only one USB port! Connecting devices like serial modems, GPS receivers, serial printers, and PDAs has never been easier.

Perfect for laptop users, the ICUSB232\_4 is light weight and compact, so you can take it with you when you're on the go. As well, the unit is fully plug and play compatible, allowing you the flexibility of hot swapping your serial devices without rebooting.

### Applications

- Connect modems, digitizer tablets, mice, bar code scanners, GPS receivers, ISDN terminal adapters, mobile phones, scanners, UPSes and POS equipment to your system

### Features

- Bus powered, no external power adapter required
- Easy Plug-and-Play installation
- Fully compliant with USB 1.1 specifications and compatible with USB 2.0

## Technical Specifications

Warranty	Lifetime
Ports	4
Bus Type	USB 2.0
Industry Standards	RS232
Industry Standards	USB 1.1
Connector Type(s)	1 - USB A (4 pin) Female
Connector Type(s)	4 - DB-9 (9 pin; D-Sub) Male
Maximum Data Transfer Rate	115000 Kbits/Sec
Serial Protocol	RS-232
Cable Length	6 feet (1.82 meters)
Communication Buffer	Dual 16 Byte hardware data buffer design buffers upstream and downstream data flow
OS Support	Windows 98SE/ME/2000/XP and Server 2003
System Requirements	One free USB port
Product Weight	0.2 lb [0.1 kg]
System and Cable Requirements	One free USB port
Shipping (Package) Weight	0.7 lb [0.3 kg]

## Certifications, Reports and Compatibility

