

2.5in Silver USB 2.0 to IDE External Hard Drive Enclosure

StarTech ID: IDE2510U2



This USB 2.0 to IDE 2.5 in. External Hard Drive Enclosure lets you transform virtually any 2.5in IDE notebook hard drive into the perfect portable storage solution.

Ideal for storing digital multimedia and other demanding applications, the IDE hard drive enclosure allows you to get the most out of your hard drive, connecting to a host computer using USB 2.0 (also backward compatible with USB 1.1), for maximum data transfer rates of up to 480Mbps.

A truly portable solution, the enclosure features lightweight yet durable aluminum construction, as well as a small form factor design that fits perfectly into your pocket or notebook bag when not in use. To eliminate the hassle of having to find a power outlet when you're ready to back up your data or load your stored files, the enclosure requires no external power supply, as it's powered through USB connection to the host computer.

Applications

- Create a fast, ultra portable external storage solution for laptops or netbooks
- Add-on storage to any USB enabled computer system
- Backup data to an external storage device
- Retrieve data from old laptop drive, or turn the unused drive into additional external storage space

Features

- Light-weight, durable aluminum construction
- High Speed USB 2.0 compliant host interface, with transfer rates up to 480 Mbps
- Power/activity LED
- Compatible with PATA (IDE) 66/100/133 Mbps drives
- Supports 2.5" form factor IDE hard drives
- Powered directly from the USB ports
- Compact, portable design
- Includes a protective carrying pouch

Technical Specifications

Warranty	2 Years
Interface	USB 2.0
Bus Type	USB 2.0
Number of Drives	1
Drive Size	2.5in
Drive Type	IDE (ATA)
Drive Installation	Fixed
Fan(s)	No
Chipset ID	Genesys Logic - GL-811E
Connector Type(s)	1 - USB Mini-B (5 pin) Female
Maximum Data Transfer Rate	480Mbps
RAID	No
Max Drive Capacity	160GB @ 5400 RPM
OS Compatibility	Windows 2000/ XP(32/64-bit)/ Server 2003(32/64-bit)/ Server 2008 R2/ Vista(32/64-bit)/ 7(32/64-bit)/ 8(32/64-bit) Mac OS X (tested up to 10.8) Linux
Color	Silver
Enclosure Type	Aluminum
Max Drive Height	0.4 in [9.5 mm]
Product Length	4.7 in [120 mm]
Product Width	3 in [75 mm]
Product Height	0.4 in [10 mm]
Product Weight	2.2 oz [62.1 g]
LED Indicators	1 - Green: Power / Red: Drive Activity
Power Adapter Included	No
Input Voltage	5 DC
Operating Temperature	05/23/2012eg;C to 605/23/2012eg;C (325/23/2012eg;F to 1405/23/2012eg;F)
Storage Temperature	-205/23/2012eg;C to 705/23/2012eg;C (-45/23/2012eg;F to 1585/23/2012eg;F)
Humidity	0~90% RH
Shipping (Package) Weight	0.5 lb [0.2 kg]
Included in Package	1 - 2.5in IDE Enclosure

Included in Package	1 - USB 2.0 Y-Cable
Included in Package	1 - Protective Case
Included in Package	1 - Screw Kit
Included in Package	1 - Mini Screwdriver
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

