

## 3.5in Black External USB IDE Hard Drive Enclosure

StarTech ID: IDE3510U2



The IDE3510U2 USB IDE Hard Drive Enclosure provides cost-effective external storage, letting you connect a 3.5in IDE hard drive to a computer through USB 2.0 - perfect for extending the useful life of older IDE hard drives.

Compatible with USB 2.0-enabled Mac and PC computers, the hard drive enclosure features an attractive aluminum and steel chassis that provides maximum durability and heat dissipation.

### Applications

- Archive or make backups to existing data for added security
- Easy add-on storage for business or personal use
- Ideal for storing data from digital cameras, DV camcorders, MP3 files, computer games or for backing up personal and work documents
- Share important files and applications between computers

### Features

- Aluminum design cools and protects hard drive
- Plug and play for USB 2.0 - can be setup in minutes, designed for easy installation
- Compact design and light weight makes the unit extremely portable
- Data transfer at rates up to 480 Mbps
- LED indicators that continuously show the operating status of the hard drive
- PC, Mac, and Linux Compatible
- Saves time - Hot-swap capability allows you to connect and disconnect drives without having to shut down computer

Technical Specifications

Warranty	2 Years
Interface	USB 2.0
Number of Drives	1
Drive Size	3.5in
Drive Type	IDE (ATA)
Drive Installation	Fixed
Fan(s)	No
Chipset ID	Initio - INIC-151
Drive Connectors	1 - IDE (40 Pin; EIDE/PATA) Female
Drive Connectors	1 - LP4 (4 pin; Molex Large Drive Power) Female
Host Connectors	1 - USB B (4 pin) Female
Type and Rate	USB 2.0 - 480 Mbit/s
RAID	No
Max Drive Capacity	750Gb
Color	Black
Enclosure Type	Aluminum and Steel
Product Length	8.7 in [222 mm]
Product Width	1.3 in [33 mm]
Product Height	4.9 in [124 mm]
Product Weight	17.6 oz [499 g]
LED Indicators	1 - Green - Power Indicator
LED Indicators	1 - Red - Drive Activity
Power Adapter Included	Yes
Input Voltage	115 AC
Output Voltage	12 DC
Output Current	2A
Center Tip Polarity	Positive
Plug Type	N
Operating Temperature	05/8/2012eg;C to 705/8/2012eg;C (325/8/2012eg;F to 1585/8/2012eg;F)
Storage Temperature	10~90%RH
Humidity	-205/8/2012eg;C to 755/8/2012eg;C (-45/8/2012eg;F to 1675/8/2012eg;F)
Shipping (Package) Weight	2.2 lb [1 kg]
Included in Package	1 - 3.5" USB 2.0 IDE Hard Drive Enclosure
Included in Package	1 - Black Enclosure Stand

Included in Package	1 - USB 2.0 Cable
Included in Package	1 - Power Adapter
Included in Package	1 - Instruction Manual

**Certifications, Reports and Compatibility**

