

InfoSafe 2.5" USB 2.0 On-The-Go External Hard Drive Enclosure

StarTech ID: IDECASE25OTG



Turn your 2.5" IDE hard drive into the ultimate USB "On-the-go" storage solution! At the touch of a button, you can copy files directly from a digital source (Camera, MP3 player, card reader etc.) to your external storage without even needing to connect to a host computer - making this the ideal solution for offloading your valuable data. Plus you can connect to a PC and use the one button backup feature to share files and make external backups. The portable and lightweight case is constructed with durable brushed aluminum to enhance durability for mobile applications. A truly portable solution for "On-the-Go" applications, IDECASE25OTG can be bus powered through USB, through the included battery pack (4 'AA' batteries required), or a 5V DC power adapter.

Applications and Solutions

- Backup your existing hard drive for extra data security
- Copy files (including images, audio, and multimedia) directly from a digital camera, MP3 player or other USB devices to the hard drive without need of a computer
- Easy add-on storage for home or office usage
- Great for storing/editing space consuming videos and high-end graphic files and making them portable
- Share files with friends/colleagues

Features

- Unique one button feature copies files from your device to the hard drive automatically
- Backwards compatible with the USB 1.1 standard (USB 2.0 device interface required to achieve maximum data transfer speeds)
- Compact battery pack keeps you running on the road
- Hot-swappable, allows for file transfers without having to reboot your computer
- Pocket-sized enclosure in a lightweight, durable brushed aluminum finish
- Supports almost any 2.5" form factor IDE hard drive

Technical Specifications

- Warranty: 1 Year warranty
- Color: Silver
- Connector Types: 1 - USB A Female
- Product Height: 0.51 in [1.3 cm]
- Product Length: 5.35 in [13.6 cm]
- Maximum Data Transfer Rate: 480000000 Mbits/Sec
- Power Adapter Included: Yes
- Carton Quantity: 18
- Shipping (Package) Weight: 0.95 lb [0.43 kg]
- Product Width: 2.95 in [7.5 cm]
- Power Adapter: 5V DC, 1.5A, positive center
- Hard Drive Compatibility: EIDE: ATA/33/66/100/133/166 drives supported(ATA/100/133/166 drives interface at ATA/66 speeds)
- Volume Format: To use on-the-go feature hard drive must be formatted with FAT32 file system. NTFS is supported but will not with on-the-go.
- Maximum Data Transfer Rate: 480 Mbps (USB 2.0)

