

InfoSafe 2.5" USB 2.0 On-The-Go External Hard Drive Enclosure

StarTech ID: IDECASE25OTG



Turn your 2.5" IDE hard drive into the ultimate USB "On-the-go" storage solution! At the touch of a button, you can copy files directly from a digital source (Camera, MP3 player, card reader etc.) to your external storage without even needing to connect to a host computer - making this the ideal solution for offloading your valuable data. Plus you can connect to a PC and use the one button backup feature to share files and make external backups. The portable and lightweight case is constructed with durable brushed aluminum to enhance durability for mobile applications. A truly portable solution for "On-the-Go" applications, IDECASE25OTG can be bus powered through USB, through the included battery pack (4 'AA' batteries required), or a 5V DC power adapter.

Applications

- Copy files (including images, audio, and multimedia) directly from a digital camera, MP3 player or other USB devices to the hard drive without need of a computer
- Backup your existing hard drive for extra data security
- Share files with friends/colleagues
- Easy add-on storage for home or office usage
- Great for storing/editing space consuming videos and high-end graphic files and making them portable

Features

- Unique one button feature copies files from your device to the hard drive automatically
- Hot-swappable, allows for file transfers without having to reboot your computer
- Pocket-sized enclosure in a lightweight, durable brushed aluminum finish
- Compact battery pack keeps you running on the road
- Supports almost any 2.5" form factor IDE hard drive
- Backwards compatible with the USB 1.1 standard (USB 2.0 device interface required to achieve maximum data transfer speeds)

Technical Specifications

Warranty	2 Years
Connector Type(s)	1 - USB A (4 pin) Female
Maximum Data Transfer Rate	480 Mbps
General Specifications	480 Mbps (USB 2.0)
General Specifications	5V DC, 1.5A, positive center
General Specifications	EIDE: ATA/33/66/100/133/166 drives supported (ATA/100/133/166 drives interface at ATA/66 speeds)
General Specifications	To use on-the-go feature hard drive must be formatted with FAT32 file system. NTFS is supported but will not with on-the-go.
Color	Silver
Product Length	5.4 in [13.6 cm]
Product Width	3 in [7.5 cm]
Product Height	0.5 in [1.3 cm]
Power Adapter Included	Yes
Shipping (Package) Weight	1 lb [0.4 kg]
Included in Package	1 - IDECASE25U2
Included in Package	1 - USB 2.0 cable with extra power connector
Included in Package	1 - Installation CD
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility



