

3.5in USB Network Attached Storage NAS External Hard Drive Enclosure

StarTech ID: IDECASE35NAS



Connect multiple computers to a single 3.5" hard drive, with the added security of configurable access privileges to protect valuable data. As much as 30% faster than similar NAS enclosures, this network attached storage hard drive enclosure is the perfect solution for adding storage to your LAN, and with support for RAID 0, 1 and JBOD, multiple hard drives can be joined for consolidated data backup.

IDECASE35NAS features plug and play installation, requires no IP address and can be installed virtually anywhere on a local area network.

As an added security feature, users require the necessary software installation prior to using, so unauthorized users won't be able to access the drive contents.

This product includes the necessary cabling to attach to your network, and is backed by StarTech.com's 2-year warranty.

Applications

- Easy add-on storage for business or personal use.
- Archive or make backups to existing data for added security.
- Share important files and applications between computers.
- Ideal for storing data from digital cameras, DV camcorders, MP3 files, computer games or for backing up personal and work documents.

Features

- Supports RAID 0, 1, and JBOD
- Supports NTFS for error-free transfer of large files and quick disk access speeds
- Customizable access privileges for greater network security
- No IP addresses or dedicated computer/server names are required for LAN connectivity
- Easy to setup once installed, Software automatically finds and configures
- Expandability- connect several hard drives using our enclosures to network and appears to users as one large drive

Technical Specifications

Warranty	2 Years
Connector Type(s)	1 - RJ-45 Female
Connector Type(s)	1 - USB B (4 pin) Female
Maximum Data Transfer Rate	480000000 Kbits/Sec
General Specifications	3"USB "A" to USB "B" Cable and 18"Cat 5e cable all included.
General Specifications	Compatible with 3.5" IDE ATA133/66/100
General Specifications	Up to 750GB
General Specifications	Windows 98SE/ME/2000 & XP; MAC OS X
Color	Black
Enclosure Type	Aluminum
Product Length	8.3 in [210 mm]
Product Width	5.7 in [14.5 cm]
Product Height	1.9 in [48 mm]
Product Weight	14.8 oz [420 g]
LED Indicators	1 - Power / Activity
Power Adapter Included	Yes
Center Tip Polarity	Positive
Shipping (Package) Weight	2.6 lb [1.2 kg]

Certifications, Reports and Compatibility

