

Portable 5.25in IEEE-1394a FireWire 400 IDE Drive Case

StarTech ID: IDECASE525F



Adding external, portable, high-speed hard disk or optical storage to your computer is easy with StarTech.com's FireWire CD drive case. This case is the perfect solution for users who need personal storage space that is completely transportable. Capable of holding 5.25 inch hard drives or optical drives, the blazing fast Firewire data transfer rate and portability make this item the perfect compliment to your PC or Mac.

Applications

- Make an IDE hard drive, CD-ROM, DVD, or CD-RW drive portable

Features

- Works with 5.25 inch IDE hard drives , CD-ROM, CD-RW, and DVD drives
- Works with PC (Windows 98SE, ME, or 2000) or Mac (OS 9 or better)
- High speed 400 MBps IEEE-1394 Firewire transfer rate
- Provides a daisy chain port for connecting additional Firewire peripherals
- A cooling fan keeps air moving through the case

Technical Specifications

Warranty	2 Years
Number of external 5.25 inch bays	1
Fans	1 - 40 mm
Connector Type(s)	2 - Firewire 400 (6 pin; IEEE 1394a) Female
Maximum Data Transfer Rate	400000000 Kbits/Sec
General Specifications	1 x 40 pin IDE connector 1 x LP4 4 pin power connector
General Specifications	Windows 98SE, ME, 2000 and Mac
Color	Beige
Enclosure Type	Plastic
Product Length	10 in [255 mm]
Product Width	6.1 in [155 mm]
Product Height	2 in [50 mm]
LED Indicators	1 - Activity
LED Indicators	1 - Power
Input Voltage	12 DC
Shipping (Package) Weight	4 lb [1.8 kg]
Included in Package	1 - Ext. 5.25" Firewire IDE CD Drive Case
Included in Package	1 - Firewire cable bag of screws
Included in Package	1 - bag of screws and keys
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

