

Portable 3.5" IEEE-1394b FireWire 800 and USB 2.0 Combo IDE Hard Drive Case

StarTech ID: IDECASEU2FB



Designed for performance users, this combination IEEE-1394b/USB 3.5 hard drive case puts you on the cutting edge of high-speed external storage. This versatile case uses two of the most popular high-performance interfaces, FireWire 800 and USB 2.0, to ensure the best performance no matter where you use it. The attractive, rugged case is designed for travel so your important data can go anywhere you do.

A fast and easy way to store data for both desktop and laptop computers, the IDECASEU2FB is perfect for users who want a versatile, high-speed storage solution.

Applications

- Easy add-on storage in a home or office environment
- Terrific for backing-up your existing hard drive for extra data security, or archiving valuable data from desktop and laptop computers
- Share and integrate important files and applications between computers
- Excellent for storing digital camera pictures, MP3 files and computer games

Features

- Equipped with 2 FireWire 800 ports and 1 USB 2.0 port
- Connects to a USB or a IEEE-1394b FireWire 800 port on your PC or Mac
- Hot-swap capabilities allows you to connect or disconnect the case without powering off your computer
- Backward compatible with the IEEE-1394a FireWire standard
- A handy LED indicator continuously shows operating status of the hard drive
- Comes complete with an IEEE-1394b FireWire 800 cable and a 3 ft. USB 2.0 cable
- Designed with an internal fan to keep your case cool
- Removable front bezel

Technical Specifications

Warranty	2 Years
Fans	1 - 40 mm
Connector Type(s)	1 - USB B (4 pin) Female
Connector Type(s)	2 - Firewire 800 (9 pin; IEEE 1394b) Female
Maximum Data Transfer Rate	800000000 Mbits/Sec
General Specifications	Plastic and steel combination
General Specifications	Windows 98SE/ME/2000/XP/Server 2003, Mac OS 9.2 and up
Color	Black
Product Length	4.8 in [123 mm]
Product Width	8.3 in [210 mm]
Product Height	1.4 in [36 mm]
Product Weight	19.5 oz [553.3 g]
LED Indicators	1 - Power / Activity
Center Tip Polarity	Positive
Shipping (Package) Weight	2.9 lb [1.3 kg]

Certifications, Reports and Compatibility

