

24in Right Angle Latching SATA Serial ATA Cable

StarTech ID: LSATA24RA2



This 24in right-angled latching SATA cable features two right-angled (female) SATA connectors, providing a simple connection to a Serial ATA drive even if space near the drive's SATA port is limited. The cable offers latching connectors, which ensure secure connections for latchable SATA hard drives and motherboards that support this feature.

Once the right-angled SATA connector has been inserted into the drive's data port, the shaft of the cable is seated flush with the rear panel of the drive, eliminating the clutter of excess cable at the connection point - an ideal solution for small or micro form factor computer cases.

The right angled SATA cable features a thin, narrow construction that helps to improve airflow within the computer case; the cable features a rugged, yet flexible design that makes it easy to make the SATA connection as needed, and is backed by StarTech.com's Lifetime Warranty.

Features

- Compliant with Serial ATA II Specifications
Fast data transfer rate of up to 6 Gbps

Technical Specifications

Warranty	Lifetime
Connector A	1 - SATA (7 pin; Data) Receptacle
Connector B	1 - SATA (7 pin; Data) Receptacle
Type and Rate	SATA III (6 Gbps)
Color	Red
Connector Style	Right Angled
Cable Length	24 in [609.6 mm]
Shipping (Package) Weight	0.1 lb [0 kg]
Included in Package	1 - 24in Right Angle Latching SATA Serial ATA Cable

Certifications, Reports and Compatibility

