

75 ft White Molded Cat5e UTP Patch Cable

StarTech ID: M45PATCH75WH



StarTech.com's Cat5e UTP Patch Cables offer reliable Ethernet connections. This 75 ft cable meets or exceeds all Category 5e specifications, and features a durable white jacket that simplifies departmental color coding while providing rugged flexibility for network connections.

To ensure long-lasting performance, our high quality Cat5e UTP Patch Cables offer PVC molded strain relief that prevents the RJ45 connector termination points from bending at sharp angles - reducing the risk of decreased network performance due to cable damage.

StarTech.com's 75 ft White Cat5e UTP Patch Cable is constructed of only top quality materials (100% copper conductors, 24 Gauge Wire, 50 micron Gold Connectors) to ensure optimum durability and performance, and is backed by our Lifetime Warranty.

Applications and Solutions

- Connects workstation to wall outlet
- Patches from hub to distribution panel

Features

- Coloured Hoods for departmental colour coding
- StarTech Category 5e patch cables are carefully constructed and tested, to keep the Near End Crosstalk (NEXT) well within acceptable limits
- StarTech Category 5e Patch cables are constructed with top quality components. Various colours & custom lengths are available.
- The Strain relief prevents the cable from being bent at sharp angles at the connector to minimize the stress at the plug termination point

Technical Specifications

- Warranty: Lifetime warranty
- Connector A: 1 - RJ45 Male
- Connector B: 1 - RJ45 Male
- Color: White
- Product Length: 74.98 ft [22.86 m]
- Maximum Cable Length: 328 ft [100 m]
- Network Cable Type: Molded
- Carton Quantity: 20
- Shipping (Package) Weight: 1.7 lb [0.77 kg]
- Connectors: RJ45 Male, RJ45 Male
- Length: 75 ft. [22.9m]
- Cable: 24 AWG, 4 pair UTP, general building use (CMG), FT4 fire rating, type CM (UL) certified, meets TIA/EIA 568B industry standards, Category 5e patch cable

