

10/100 Multi Mode Fiber to Ethernet Media Converter SC 2km with PoE

StarTech ID: MCM110SC2P



This 10/100Base to 100Base-FX Multimode SC Fiber Ethernet Media Converter supports a maximum fiber cable distance of 2km, ensuring a highly reliable signal for ideal network connectivity and performance.

The converter features Power over Ethernet support that allows the converter to draw power from a PoE network, delivering the freedom to use the converter in environments and scenarios where additional standard power options are unavailable.

Rather than paying for expensive installations of power wire (at drop points that may have them), running PoE requires only standard network cable (e.g. [Cat5e cable](#)), eliminating cost and hassle.

Backed by our 2-year warranty, the 10/100Base to 100Base-FX Multimode Fiber Ethernet Media converter features a durable design to help ensure reliability and long-lasting performance.

Applications and Solutions

- Designed for large, high speed bandwidth requirements of demanding workgroups needing expansion of their fast Ethernet Network.
- Works well in industrial applications where standard power outlets are not available, or are too costly to install

Features

- Supports IEEE 802.3 10Base-T, 802.3u 100Base-TX and 100Base-FX industry standards
- Auto detects half/full duplex transfer mode from the TX port.
- It's compact design and weight makes it portable and unobtrusive to carry
- Led Indicators
- Supports a maximum multimode fiber optic cable distance of 2km
- Auto – negotiation of 10/100 Mbps and Auto – Crossover for TX port.
- Provides switch configuration of half/full duplex transfer mode for FX port.
- Supports Q in Q double tagged frame transparent
- Forward 1600 bytes (Max.) packets
- Supports IEEE 802.1q Tag VLAN pass thru
- Support flow control (Pause) and Link Fault Pass through (LFP)
- Supports 802.3af Power over Ethernet (only FMC-10/100P)
- Fiber Support: Cable Type- 62.2/125µm, 50/125µm - 2km Range
- Can be powered over RJ45 ethernet with a PoE enabled network

Technical Specifications

- Warranty: 2 Years
- Product Height: 0.79 in [20 mm]
- Humidity: 10~90% RH
- LED Indicators: 1 - Power
- LED Indicators: 1 - 10/100 Operating Mode
- LED Indicators: 1 - POE Enabled
- LED Indicators: 1 - Full/Half Duplex Mode
- LED Indicators: 1 - Fiber Activity/Link
- LED Indicators: 1 - Ethernet Activity/Link
- Product Length: 3.74 in [95 mm]
- Maximum Data Transfer Rate: 10/100 Mbps
- Max Transfer Distance: 1.24 Miles (2 km)
- Operating Temperature: 0°C to 50°C (32°F to 122°F)
- Output Current: 400mA
- Carton Quantity: 25
- Storage Temperature: -10°C to 70°C (14°F to 158°F)
- Wave Length: 1310nm
- Shipping (Package) Weight: 0.62 lb [0.28 kg]
- Product Weight: 3.18 oz [90 g]
- Product Width: 2.95 in [75 mm]