

## 10 ft Coax High Resolution VGA Monitor Extension Cable - HD15 M/F

StarTech ID: MXT101HQ10



This 10ft High Resolution VGA Extension Cable is designed to provide the highest video quality possible through VGA.

Ideally suited for high resolution VGA applications, this high quality male to female coaxial VGA extension cable helps to eliminate picture "ghosting" and fuzzy images inherent to non-coaxial cables, and provides superior EMI interference protection by using ferrite cores near the connector ends.

### Applications and Solutions

- Connects PC's VGA port to a StarView
- Extends VGA/SVGA monitor cable

## Features

- Ferrite core eliminates EMI
- Ideal for high resolution monitors (1024x768 and above)
- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Molded connector ends with strain relief
- Triple-coaxial + twisted-pair wire for crystal clear display

## Technical Specifications

- Warranty: Lifetime warranty
- Color: Black
- Carton Quantity: 50
- Shipping (Package) Weight: 0.95 lb [0.43 kg]
- Cable Length: 10 ft [3.05 m]
- Connector A: 1 - 15 pin High Density D-Sub (VGA) Male
- Connector B: 1 - 15 pin High Density D-Sub (VGA) Female

