

75 ft Coax High Resolution VGA Monitor Extension Cable - HD15 M/F
StarTech ID: MXT101HQ75



This 75ft High Resolution VGA Extension Cable is designed to provide the highest video quality possible through VGA.

Ideally suited for high resolution VGA applications, this high quality male to female coaxial VGA extension cable helps to eliminate picture "ghosting" and fuzzy images inherent to non-coaxial cables, and provides superior EMI interference protection by using ferrite cores near the connector ends.

Features

- Ferrite core eliminates EMI interference
- Ideal for high resolution monitors (1024x768 and above)
- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Molded connector ends with strain relief
- Triple-coaxial + twisted-pair wire for crystal clear display

Technical Specifications

- Warranty: Lifetime warranty
- Connector A: 0 - High Density DB15 Male
- Cable Length: 75 ft [22.86 m]
- Connector B: 0 - High Density DB15 Female
- Color: Black
- Cable Jacket Type: PVC - Polyvinyl Chloride
- Shipping (Package) Weight: 4.82 lb [2.18 kg]
- Wire Gauge: 28 AWG
- Carton Quantity: 8

