

## 75 ft Coax High Resolution VGA Monitor Extension Cable - HD15 M/F

StarTech ID: MXT101HQ75



This 75ft High Resolution VGA Extension Cable is designed to provide the highest video quality possible through VGA.

Ideally suited for high resolution VGA applications, this high quality male to female coaxial VGA extension cable helps to eliminate picture "ghosting" and fuzzy images inherent to non-coaxial cables, and provides superior EMI interference protection by using ferrite cores near the connector ends.

### Features

- Ideal for high resolution monitors (1920x1200 and above)
- Triple-coaxial + twisted-pair wire for crystal clear display
- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Ferrite core eliminates EMI interference
- Molded connector ends with strain relief

### Technical Specifications

Warranty	Lifetime
Cable Jacket Type	PVC - Polyvinyl Chloride
Connector A	VGA (15 pin; High Density D-Sub) Male
Connector B	VGA (15 pin; High Density D-Sub) Female
Color	Black
Wire Gauge	28 AWG
Cable Length	75 ft [22.9 m]
Shipping (Package) Weight	4.8 lb [2.2 kg]
Included in Package	75 ft Coax High Resolution VGA Monitor Extension Cable - HD15 M/F

Certifications, Reports and Compatibility

